# **K**ØSTER

# // Application

#### Horizontal drilling in the bed joint



Installation of the horizontal barrier



Diffusion open KÖSTER Restoration Plasters



## KÖSTER at your service – worldwide.











### // Contact us

KÖSTER BAUCHEMIE AG Dieselstraße 1–10 · 26607 Aurich Tel.: +49 4941 9709 0

E-Mail: info@koster.eu

www.koster.eu

Follow us on social media:

















#### KÖSTER Crisin 76 Very low viscosity synthetic resin for waterproofing against rising damp (wicking moisture).



### KÖSTER Suction Angle

Plastic angle for the pressureless and material saving installation of horizontal barriers.



### KÖSTER Capillary Rods

The KÖSTER
Capillary Rod
releases the
injection liquid
evenly and directly
to the masonry.

# The advantages of the Suction Angle System:

- Can be applied to perforated brick and cracked or hollow masonry without having to fill the voids beforehand
- No subsequent injections required
- One-time installation, success guaranteed
- Easy installation, horizontal drilling
- Reusable bottles and suction angles

# Key features of KÖSTER Crisin 76 at a glance:

- Suitable even in cases of high moisture contents < 95 %
- Suitable even in cases of high salt contents and for most types of salts (sulfates, nitrates, chlorides)
- · Solvent free
- The treated substrate does not have to be alkaline for the material to react
- No prior or subsequent drying of the wall necessary, even in case of high moisture contents
- Can not be diluted with water / is not water soluble
- Resistant against most ordinary aggressive substances that are encountered in masonry such as acids, alkalis and salts
- · Fast reaction, immediately effective
- Not bio-degradable
- Does not cause or promote corrosion of steel reinforcements
- Low density (0.91 g/cm³); penetrates deeply even into the smallest capillaries of the construction material
- The cured material is elastic
- · Does not dissolve any salts
- Proven to be effective for more than 30 years